

Electrical module VMPA1-MPM-EMM-4

Part number: 537987

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	4
Max. number of valve coils	4
Nominal pick-up current per solenoid coil	80 mA up to 25 ms
Nominal current with current reduction	25 mA after 25 ms
Corrosion resistance class CRC	(when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Material housing	POM
Note on materials	RoHS-compliant