

Plug socket NTSD-GD-9-M12-5POL-RK

Part number: 538999

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------|---|
| Electrical connection | 5-pin Straight plug connector/screw terminal |
| Permissible current load | 3 A |
| Permissible cable diameter | 6 mm ... 8 mm |
| Connection cross section | 0.75 mm ² |
| Degree of protection | IP67 |
| Ambient temperature | -40 °C ... 85 °C |
| Note on materials | RoHS-compliant |
| Material housing | PA |
| Housing colour | Black |