

Plug socket MSSD-C-M16

Part number: 539709

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Frequency of connection	50
Type of mounting	On solenoid valve via M3 central screw
Mounting position	optional
Product weight	38 g
Electrical connection	3-pin Angled socket Type A To DIN EN 175301-803 Square design
Cable fitting	M16
Permissible cable diameter	6 mm ... 8 mm
Connection cross section	1.5 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C ... 115 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material seals	HNBR