

Pressure gauge kit DPA-40-10-MA-SET

Part number: 540781

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Symbol	00991463
Conforms to standard	EN 837-1
Nominal size of pressure gauge	27
Design	Bourdon tube pressure gauge
Type of mounting	Via male thread
Operating pressure	10 bar
Measurement accuracy class	4
Degree of protection	IP43
Ambient temperature	5 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Mounting position	optional
Pneumatic connection	R1/8
Product weight	16 g