

AS-i module

ASI-4DI3DO-M12X2-5POL-Z

Part number: 542125



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| CE mark (see declaration of conformity) | To EU EMC Directive To EU Explosion Protection Directive (ATEX) In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| KC mark | KC-EMV |
| Approval | c UL us listed (OL) |
| Explosion protection | Zone 2 (ATEX) Zone 2 (UKEX) Zone 22 (ATEX) Zone 22 (UKEX) |
| ATEX category gas | II 3G |
| ATEX category dust | II 3D |
| Explosion protection certification outside the EU | EPL Dc (GB) EPL Gc (GB) |
| Explosion ignition protection type for gas | Ex ec IIC T4 Gc X |
| Explosion ignition protection type for dust | Ex tc IIIC T115°C IP67 Dc X |
| Explosion ambient temperature | -5°C ≤ Ta ≤ +50°C |