



Regulator plate VMPA1-B8-R2C2-C-10

Part number: 543340

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|------------------------------------|--|
| Construction width | 10.5 mm |
| Mounting position | optional |
| Vertical pneumatic linkage | Pressure regulator for 2 |
| Controller function | Output pressure constant With secondary venting |
| Symbol | 00992003 |
| Selection of pressure gauge | Possible |
| Pressure regulation range | 2 bar ... 8.5 bar |
| Inlet pressure 1 | 0.5 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 To IEC 60529 |
| Ambient temperature | -5 °C ... 50 °C |
| Max. tightening torque | 0.25 Nm |
| Product weight | 73.8 g |
| Mounting with vertical stacking | On manifold sub-base |
| Pressure gauge connection | M5 |
| Note on materials | RoHS-compliant |
| Material control panel | PA |
| Material seals | NBR |
| Material regulator housing | PA |