

Multi-pin node VABE-S6-1LF-C-M1-R19

Part number: 543415

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Mounting position | optional |
| Max. number of valve positions | 16 with monostable valves 8 with bistable valves |
| Nominal operating voltage DC | 24 V |
| Permissible voltage fluctuations | +/- 10 % |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 NEMA 4 |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 539 g |
| Electrical control | Multi-pin plug |
| Electrical connection | 19-pin Plugs To CNOMO E03.62.530.N |
| Material cover | PA |
| Material housing | Die-cast aluminium |