

Adapter NEFC-M12G5-0.3-U1G5

Part number: 547432

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	Screw-in
Electrical connection	5-pin M12x1 Plugs
Cable length	0.3 m
Cable structure	4 x 0.34 mm ²
Degree of protection	IP20
Ambient temperature	-5 °C ... 50 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
Material cable sheath	PUR
Material housing	ABS
Material electrical contact	Gold-plated brass