

Solenoid coil MD-2-24VDC-PA

Part number: 549903

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Duty cycle	100%
Characteristic coil data	24 V DC: 6.8 W
Permissible voltage fluctuations	+/- 10 %
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Max. tightening torque for fitting	0.5 Nm
Product weight	110 g
Electrical connection	To DIN EN 175301-803
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper