


Service unit combination MSB4N-1/4:J1D7A1-WP

Part number: 550491

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 4 |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Vertical +/-5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manually rotating |
| Design | Standard mist lubricator |
| Controller function | Output pressure constant Via primary pressure compensation With secondary venting With return flow function |
| Bowl guard | Plastic bowl guard |
| Symbol | 00991597 |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | With pressure gauge |
| Operating pressure | 4.5 bar ... 10 bar |
| Pressure regulation range | 4 bar ... 9 bar |
| Standard nominal flow rate (standardised to DIN 1343) | 750 l/min |
| Characteristic coil data | 24 V DC: 1.8 W |
| Operating medium | Inert gas |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Suitable for use with food | See supplementary material information |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Media temperature | -10 °C ... 50 °C |
| Ambient temperature | -10 °C ... 50 °C |
| Product weight | 1600 g |
| Type of mounting | With accessories |
| Pneumatic connection, port 1 | 1/4 NPT |
| Pneumatic connection, port 2 | 1/4 NPT |
| Pneumatic connection, port 3 | G1/4 |
| Material housing | Die-cast aluminium |
| Material bowl | PC |