

Fibre-optic cable SOOC-TB-P-C5-2-R10

Part number: 552828

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Note on materials	RoHS-compliant
Measurement method	Fork light barrier
Min. object diameter	0.2 mm
Fibre-optic - special feature	Fork light barrier
Operating distance	5 mm
Ambient temperature	-55 °C ... 70 °C
Head size	Rectangle 41x15x7 mm Fork pit 5x29 mm
Fibre-optic length	2 m
Min. bending radius	10 mm
Outside diameter	1.25 mm
Material housing	ABS
Material fibre-optic	PE
Degree of protection	IP66
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III