


Manifold rail MHJ9-P16

Part number: 553125

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	10 mm
Max. number of valve positions	16 Versions according to customer specifications possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight	428 g
Type of mounting	Via mounting bracket
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	M7
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy, anodised