

Bellows kit DADB-V6-32-S10-50

Part number: 553271

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|---|
| Outside diameter | 38 mm |
| Size | 32 |
| Stroke range | 10 mm ... 50 mm |
| Piston rod extension | 29 mm |
| Design | Round |
| Mounting position | optional |
| Design | With ducted exhaust air |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media resistance | Dust Chips Oils Grease Petrol |
| Degree of protection | IP54 |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 29 g |
| Type of mounting | Push-on Via threaded pin |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Material adapter components | PA-reinforced |
| Material seals | NBR |
| Material bellows | NBR |
| Material threaded pin | High-alloy stainless steel |