

Bellows kit DADB-V6-100-S251-300

Part number: 553379

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	93 mm
Size	100
Stroke range	251 mm ... 300 mm
Piston rod extension	74 mm
Design	Round
Mounting position	optional
Design	With ducted exhaust air
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C ... 80 °C
Product weight	255 g
Type of mounting	Push-on Via threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel