

Bellows kit DADB-S1-32-S251-300

Part number: 553449

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	38 mm
Size	32
Stroke range	251 mm ... 300 mm
Piston rod extension	97 mm
Design	Round
Mounting position	optional
Design	With ducted exhaust air
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C ... 80 °C
Product weight	79 g
Type of mounting	Via threaded pin Via female thread
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel