

# Plastic tubing PAN-6X1-RT

Part number: 553925

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	6 mm
Flow-relevant bending radius	32 mm
Inside diameter	4 mm
Min. bending radius	14 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa ... 1.9 MPa
Temperature-dependent operating pressure	-0.95 bar ... 19 bar
Temperature-dependent operating pressure	-13.775 psi ... 275.5 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 80 °C
Product weight according to length	0.016 kg/m
Pneumatic connection	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm
Colour	Red
Shore hardness	D 55 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A