

Manifold rail VABM-C8-12E-G14-16-M1

Part number: 557665

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|-------------------------|
| Grid dimension | 12 mm |
| Max. number of valve positions | 16 |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Max. tightening torque for valve mounting | 0.6 Nm |
| Max. tightening torque wall mounting | 5 Nm |
| Product weight | 1093 g |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | G1/4 |
| Pneumatic connection, port 5 | G1/4 |
| Note on materials | RoHS-compliant |
| Material manifold rail | Wrought aluminium alloy |