

# Plastic tubing PLN-12X1,75-SI

Part number: 558215

FESTO



 General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Outside diameter  | 12 mm  |
| Flow-relevant bending radius                              | 65 mm  |
| Inside diameter   | 8.4 mm   |
| Min. bending radius                                       | 23 mm  |
| Temperature-dependent operating pressure                  | -0.095 MPa ... 1.4 MPa   |
| Temperature-dependent operating pressure                  | -0.95 bar ... 14 bar   |
| Temperature-dependent operating pressure                  | -13.775 psi ... 203 psi  |
| Note on operating pressure                                | Water: max. 0.6 MPa at 0 - 50 °C   |
| Approval  | German Technical Control Board (TÜV)   |
| Certificate issuing authority                             | B 013277 0527 00   |
| Operating medium  | Compressed air to ISO 8573-1:2010 [7:-:-]<br>Water (liquid, ice-free)                    |
| LABS (PWIS) conformity                                    | VDMA24364-B2-L   |
| Cleanroom suitability, measured according to ISO 14644-14 | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Suitable for use with food                                | See supplementary material information   |
| Ambient temperature                                       | -30 °C ... 80 °C   |
| Product weight according to length                        | 0.054 kg/m   |
| Pneumatic connection                                      | For push-in connector outside diameter of 12 mm  |
| Colour  | Silver   |
| Note on materials   | RoHS-compliant   |
| Material tubing   | PE   |