

# Connecting cable VMPAL-KM-S-SD25-IP67-2.5

Part number: 560419

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Product weight	645 g
Electrical connection	Cable with plug
Cable length	2.5 m
Cable characteristic	Standard
Min. cable bending radius	122 mm
Cable diameter	10.2 mm
Cable structure	25 x 0.34 mm <sup>2</sup>
Degree of protection	IP67 To IEC 60529
Ambient temperature with moving cable	-5 °C ... 80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	PVC