

# Hood VMPAL-KM-SD25-IP67-0

Part number: 560428

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Product weight	100 g
Electrical connection	Pre-assembled
Permissible cable diameter	5 mm ... 13 mm
Connection cross section	0.2 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>
Degree of protection	IP67 To IEC 60529
Ambient temperature	-5 °C ... 80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress