

Hood VMPAL-KM-SD44-IP67-0

Part number: 560429

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Product weight	102 g
Electrical connection	Pre-assembled
Permissible cable diameter	5 mm ... 13 mm
Connection cross section	0.14 mm ² ... 0.34 mm ²
Degree of protection	IP67 To IEC 60529
Ambient temperature	-5 °C ... 80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress