


End plate VMPAL-EPL-FL40-IP40

Part number: 560942

FESTO



 General operating condition

Data sheet

Feature	Value
Width	43 mm
Length	107.3 mm
Max. number of valve positions	32
Valve terminal structure	Valve sizes can be mixed
Max. number of valve coils	32
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Note on degree of protection	In mounted state
Ambient temperature	-5 °C ... 50 °C
Product weight	190 g
Electrical connection 1, function	Multi-pin
Electrical connection 1, connection type	Plug
Electrical connection 1, connector system	Connection pattern FC
Electrical connection 1, number of connections/cores	40
Note on materials	RoHS compliant
Material end plate	Die-cast aluminium Reinforced PA