


Power supply module VMPAL-SP-QS12

Part number: 560952

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	23.2 mm
Length	107.3 mm
Integrated function	With electrical interlinking module
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	50 g
Pneumatic connection, port 1	For tubing outer diameter of 12 mm
Note on materials	RoHS-compliant
Material supply module	Wrought aluminium alloy PA-reinforced