

Plate VMPAL-EG

Part number: 560956

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	20.5 mm
Length	107.3 mm
Integrated function	Ducted exhaust air
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pressure regulation range	0.5 bar ... 5 bar
Inlet pressure 1	0.5 bar ... 10 bar
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	30 g
Pneumatic connection 3/5 combined	For 20 mm cartridge
Note on materials	RoHS-compliant
Material plate	PA