

Electrical interlinking module VMPAL-EVAP-10-2

FESTO

Part number: 560962



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|---|
| Valve size | 10 mm |
| Max. number of valve positions | 1 |
| Max. number of valve coils | 2 |
| Integrated function | Colour-coded assignment of the valve function |
| Nominal operating voltage DC | 24 V |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 9 g |
| Housing colour | Black |
| Material housing | PA |
| Note on materials | RoHS-compliant |