

Electrical interlinking module VMPAL-EVAP-20-1

Part number: 560965

FESTO

 [General operating condition](#)

Data sheet

Feature	Value
Valve size	20 mm
Max. number of valve positions	1
Max. number of valve coils	1
Integrated function	Colour-coded assignment of the valve function
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	14 g
Housing colour	grey
Material housing	PA
Note on materials	RoHS-compliant