

Swivel flange SNGB-200-B

Part number: 562455

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Size | 200 |
| Based on standard | ISO 15552 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 90 °C |
| Product weight | 10020 g |
| Note on materials | RoHS-compliant |
| Material mounting | Steel Galvanised |
| Material bolt | Galvanised steel |
| Material sleeve | Steel |
| Material bearing | Polymer |
| Material disc | Galvanised steel |
| Material screws | Galvanised steel |
| Material lock | Spring steel, galvanised |