

Solenoid coil VACC-S13-18-A1-2U

Part number: 562891

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Switching position indicator	no
Duty cycle	100%
Insulation material class	H
Characteristic coil data	110 V DC: 1.8 W 110 V AC: 50/60 Hz, power 1.8 VA
Permissible voltage fluctuations	-15%/+10%
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	210 g
Electrical connection	Type A Plugs To EN 175301-803
Note on materials	RoHS-compliant
Material solenoid coil	PA UP