

# Pressure gauge PAGN-40-1.6M-P10-CPA

Part number: 563737

FESTO



 [General operating condition](#)

## Data sheet

| Feature                             | Value  |
|-------------------------------------|--|
| Indicating range                    | 0 MPa ... 1.6 MPa  |
| Symbol                              | 00991463   |
| Conforms to standard                | EN 837-1   |
| Nominal size of pressure gauge      | 40   |
| Approval                            | CPA  |
| Explosion protection                | The information in the certificate must be observed!<br>Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Design                              | Bourdon tube pressure gauge  |
| Type of mounting                    | In-line installation   |
| Operating medium                    | Inert gases<br>Neutral fluids  |
| Note on operating and pilot medium  | No acetylene<br>No oxygen  |
| Operating pressure                  | 0 MPa ... 1.6 MPa  |
| Operating pressure                  | 0 bar ... 16 bar   |
| Operating pressure                  | 0 psi ... 232 psi  |
| Alternating load factor             | 0.66   |
| Measurement accuracy class          | 2.5  |
| Degree of protection                | IP43   |
| Media temperature                   | -20 °C ... 60 °C   |
| Ambient temperature                 | -20 °C ... 60 °C   |
| LABS (PWIS) conformity              | VDMA24364-B1/B2-L  |
| Note on materials                   | RoHS-compliant   |
| Position of connection              | Centred, rear side   |
| Pneumatic connection                | Cartridge 10 mm  |
| Material in contact with the medium | Brass  |
| Material screwed plug               | Brass  |
| Material housing                    | ABS  |
| Material screen                     | PS   |
| Housing colour                      | Black  |

| Feature        | Value |
|----------------|-------|
| Product weight | 50 g  |