

Blanking plug QBC-5/32H-U

Part number: 564784

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Mounting position	optional
Design	Blanking plug
Size of pack	10
Design	Push-pull principle
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C ... 60 °C
Product weight	0.992 g
Pneumatic connection, port 1	Push-in sleeve Ø 5/32"
Ambient temperature	32 °F ... 140 °F
Note on materials	RoHS-compliant
Material housing	POM