

# Blanking plug QBC-1/2H-U

Part number: 564789

FESTO



 General operating condition

## Data sheet

| Feature                                       | Value                                     |
|---|---|
| Size  | Standard                                  |
| Mounting position                             | optional                                  |
| Design  | Blanking plug                             |
| Size of pack                                  | 10  |
| Design  | Push-pull principle                       |
| Operating pressure complete temperature range | -0.095 MPa ... 1 MPa                      |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar                      |
| Operating pressure complete temperature range | -13.775 psi ... 145 psi                   |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium            | Lubricated operation possible             |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                  |
| LABS (PWIS) conformity                        | VDMA24364 zone III                        |
| Ambient temperature                           | 0 °C ... 60 °C                            |
| Product weight                                | 3.005 g                                   |
| Pneumatic connection, port 1                  | Push-in sleeve Ø 1/2"                     |
| Ambient temperature                           | 32 °F ... 140 °F                          |
| Note on materials                             | RoHS-compliant                            |
| Material housing                              | POM                                       |