

Push-in L-connector CRQSL-1/2T-U

Part number: 565349

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal size	10.998 mm
Tubing insertion depth	19.5 mm
Mounting position	optional
Design	L-shape
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.095 MPa ... 1.4 MPa
Operating pressure complete temperature range	-0.95 bar ... 14 bar
Operating pressure complete temperature range	-13.775 psi ... 203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight	50.491 g
Suitable cables	PFAN
Pneumatic connection, port 1	For tubing O.D. 1/2"
Pneumatic connection, port 2	For tubing outside diameter of 1/2"
Ambient temperature	-4 °F ... 302 °F
Colour of release ring	Silver
Note on materials	RoHS-compliant
Material housing	High-alloy stainless steel
Material release ring	High-alloy stainless steel
Material tubing seal	FPM
Material tubing clamp component	High-alloy stainless steel