

Cable connector NETC-M-M20-KA

Part number: 568279

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-20 °C ... 100 °C
Degree of protection	IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
Size	M20x1.5
Cable diameter	5 mm ... 13 mm
Colour	Silver
Material cable gland	Process automation
Material seals	EPDM
Product weight	103 g
Size of pack	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Corrosion resistance class CRC	3 - high corrosion stress