

# Plastic tubing PAN-MF-16X2-SW

Part number: 570363

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	16 mm
Flow-relevant bending radius	130 mm
Inside diameter	12 mm
Min. bending radius	75 mm
Conforms to standard	DIN 73378-PA12-PHL
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa ... 1.9 MPa
Temperature-dependent operating pressure	-0.95 bar ... 19 bar
Temperature-dependent operating pressure	-13.775 psi ... 275.5 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Mineral oil
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-60 °C ... 100 °C
Product weight according to length	0.09 kg/m
Pneumatic connection	For push-in connector O.D. 16 mm
Colour	Black
Shore hardness	D 65 +/-3
Note on materials	RoHS-compliant
Material tubing	PA12-P