

End plate VMPAL-EPL-CPX

Part number: 570783

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	40 mm
Length	107.3 mm
Max. number of valve positions	32
Valve terminal structure	Valve sizes can be mixed
Max. number of valve coils	32
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP67
Note on degree of protection	In assembled state
Ambient temperature	-5 °C ... 50 °C
Product weight	130 g
Electrical connection 1, function	Fieldbus
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	Internal for CPX
Note on materials	RoHS-compliant
Material end plate	Die-cast aluminium PA-reinforced