

Adapter VAVE-C8-1R8

Part number: 571686

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------|--|
| Signal status display | LED |
| Nominal operating voltage DC | 24 V |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 To IEC 60529 |
| Ambient temperature | -5 °C ... 60 °C |
| Mounting position | optional |
| Tightening torque | 0.25 Nm |
| Product weight | 3.5 g |
| Electrical connection | M8/- Plug connector/socket |
| Protective conductor connection | Not available |
| Type of mounting | On solenoid valve via M2 central screw |
| Note on materials | RoHS-compliant |
| Material housing | PA |
| Material electrical contact | Bronze |