

# Adapter VAVE-C8-1R1

Part number: 573194

FESTO



 [General operating condition](#)

## Data sheet

| Feature                         | Value                                  |
|---------------------------------|--|
| Signal status display           | LED                                    |
| Nominal operating voltage DC    | 24 V                                   |
| Corrosion resistance class CRC  | 2 - Moderate corrosion stress          |
| LABS (PWIS) conformity          | VDMA24364-B1/B2-L                      |
| Degree of protection            | IP65<br>To IEC 60529                   |
| Ambient temperature             | -5 °C ... 60 °C                        |
| Mounting position               | optional                               |
| Tightening torque               | 0.25 Nm                                |
| Product weight                  | 3.5 g                                  |
| Electrical connection           | M8/-<br>Plug connector/socket          |
| Protective conductor connection | Not available                          |
| Type of mounting                | On solenoid valve via M2 central screw |
| Note on materials               | RoHS-compliant                         |
| Material housing                | PA                                     |
| Material electrical contact     | Bronze                                 |