


Intermediate plate VABF-S4-2-S

Part number: 573200

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Construction width	18 mm
Based on standard	ISO 15407-2
Mounting position	optional
Symbol	00992864
Operating pressure	0.3 MPa ... 1 MPa
Operating pressure	3 bar ... 10 bar
CE mark (see declaration of conformity)	To EU Low Voltage Directive
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	203.5 g
Mounting with vertical stacking	On manifold sub-base On individual sub-base
Pilot air port 14	Sub-base size 18 mm to ISO 15407-2
Pneumatic connection, port 1	Sub-base size 18 mm to ISO 15407-2
Pneumatic connection, port 4	Sub-base size 18 mm to ISO 15407-2
Pneumatic connection, port 5	Sub-base size 18 mm to ISO 15407-2
Note on materials	RoHS-compliant
Material plate	Wrought aluminium alloy