

Manifold rail VABM-L1-10G-G18-5-GR

Part number: 573424

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Grid dimension | 10.5 mm |
| Mounting position | optional |
| Max. number of valve positions | 5 |
| Approval | c UL us - Recognized (OL) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Product weight | 363 g |
| Pilot air port 12/14 | M5 |
| Pilot exhaust port 82/84 | M5 |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 3 | G1/8 |
| Pneumatic connection, port 5 | G1/8 |
| Note on materials | RoHS-compliant |
| Material manifold rail | Wrought aluminium alloy |