

# Manifold rail VABM-L1-10G-G18-7-GR

Part number: 573426

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Grid dimension	10.5 mm
Mounting position	optional
Max. number of valve positions	7
Approval	c UL us - Recognized (OL)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 60 °C
Product weight	431 g
Pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 5	G1/8
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy