


# Adapter VMPAL-F14-G1/8

Part number: 574084

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size of pack	10
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Operating pressure	-13.05 psi ... 145 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	35 g
Pneumatic connection, port 1	Cartridge 14 mm
Pneumatic connection, port 2	G1/8
Note on materials	RoHS-compliant
Material housing	Wrought aluminium alloy