

# Connecting cable NEBV-S1G25-K-10-N-LE25-S6

Part number: 575419

FESTO



 General operating condition

## Data sheet

Feature	Value
Based on standard	DIN 47100
Cable designation	Without inscription label holder
Frequency of connection	50
Product weight	1820 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	Sub-D
Electrical connection 1, number of connections/cores	25
Electrical connection 1, used connections/cores	25
Electrical connection 1, type of mounting	2x screw 4-40 UNC
Electrical connection 1, connection pattern	00995642
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	25
Electrical connection 2, used connections/cores	25
Operational voltage range DC	0 V ... 30 V
Current rating at 40° C	2.6 A
Immunity to surge	2.4 kV
Reverse polarity protection	yes
Cable length	10 m
Cable characteristic	Standard
Test conditions cable	Test conditions on request
Bending radius, fixed cable	≥42 mm
Bending radius, moving cable	≥126 mm
Cable diameter	10.2 mm
Cable diameter tolerance	± 0.25 mm
Cable structure	25 x 0.34 mm <sup>2</sup>
Nominal cross section conductor	0.34 mm <sup>2</sup>
Wire ends	Cut off bluntly
Degree of protection	IP40
Note on degree of protection	In assembled state
Ambient temperature	-35 °C ... 80 °C
Ambient temperature with moving cable	-5 °C ... 80 °C

<b>Feature</b>	<b>Value</b>
Storage temperature	-25 °C ... 75 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	2
Corrosion resistance class CRC	0 - No corrosion stress
Material cable sheath	PVC
Cable sheath colour	Grey
Material housing	PC-reinforced
Housing colour	Black
Material screws	Nickel-plated brass
Material electrical contact	Bronze Bronze
Material insulating sheath	PVC