

Mounting kit SAMH-S-N8-S-MK

Part number: 575815

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	For T-slot
Note on materials	RoHS-compliant
Ambient temperature	-40 °C ... 85 °C
Type of mounting	Snapping in Screw-clamped Insertable in the slot from above
Max. tightening torque	0.6 Nm
Product weight	1.88 g
Material cover cap	PA
Material clamping block	High-alloy steel
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L