

# Push-in sleeve NPQH-D-S12-E-P10

Part number: 578321

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Standard
Nominal size	10 mm
Mounting position	optional
Design	Straight design
Size of pack	10
Symbol	00997424
Operating pressure complete temperature range	-0.095 MPa ... 2 MPa
Operating pressure complete temperature range	-0.95 bar ... 20 bar
Operating pressure complete temperature range	-13.775 psi ... 290 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certificate issuing authority	NSF C0523185
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See declaration of conformity NSF/ANSI 169
Ambient temperature	0 °C ... 150 °C
Product weight	16.1 g
Pneumatic connection, port 1	Push-in sleeve Ø 12 mm
Pneumatic connection, port 2	Push-in sleeve Ø 12 mm
Note on materials	RoHS-compliant
Material housing	Brass, chemically nickel-plated