

Pneumatic terminal LT-2-PK-3-DA

Part number: 5866

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Operating pressure	0.1 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	5.2 g
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant