

Sealing cap CV-PK-6-B

Part number: 6215

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size of pack | 10 |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Pneumatic connection, port 1 | For tubing outer diameter of 8 mm For barbed fitting I.D. 6 mm with union nut |
| Note on materials | RoHS-compliant |
| Material cap | TPE-U(PU) |