


Elbow quick connector GCK-3/8-PK-9-KU

Part number: 6272

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	8 mm
Mounting position	optional
Design	L-shape
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection, port 1	Male thread R3/8
Pneumatic connection, port 2	For barbed fitting inside diameter of 9 mm with nut
Material union nut	POM
Material screwed plug	POM
Note on materials	RoHS-compliant