

Silencer U-3/8-B

Part number: 6843

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Symbol	00991473
Operating pressure complete temperature range	0 MPa ... 1 MPa
Operating pressure complete temperature range	0 bar ... 10 bar
Operating pressure complete temperature range	0 psi ... 145 psi
Flow rate to atmosphere	5800 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	80 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	37 g
Pneumatic connection	G3/8
Material shock absorber insert	PE
Material screwed plug	Aluminium
Note on materials	RoHS-compliant
Material housing	Aluminium