

Multi-plug KSV-32-B

Part number: 7560

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------------------|--|
| Nominal size | 4 mm |
| Operating pressure | -0.95 bar ... 16 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7::-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 374 g |
| Max. number of connections | 32 |
| Pneumatic connection | PK-2 PK-3 PK-4 |
| Colour | Grey |
| Note on materials | RoHS-compliant |