


Sub-base VMPA14-IC-AP-S-1

Part number: 8023667

FESTO



 General operating condition

Data sheet

Feature	Value
Width	24.4 mm
Length	107.3 mm
Grid dimension	14.9 mm
Operating pressure	0.3 MPa ... 0.8 MPa
Operating pressure	3 bar ... 8 bar
Pilot pressure	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Approval	c UL us - Recognized (OL)
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	150 g
Electrical connection	M8 Plugs
Mounting method for sub-base	With through-hole
Pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	M7 G1/8
Pneumatic connection, port 2	M7 G1/8
Pneumatic connection, port 3	M7 G1/8
Pneumatic connection, port 4	M7 G1/8
Pneumatic connection, port 5	M7 G1/8
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium